

Electronic outside micrometer

With hardened tips

Mitutoyo

Application:

For measuring grooves, distances etc.

Execution:

- measuring faces made of hardened steel
- ABS function
- HOLD (measured value storage)
- Origin (measurement presetting)
- IP65
- Digimatic

Advantage:

- Accesses hard-to-reach measuring points

Delivery:

Including box, set standard (from 25 mm) wrench, battery



Art. no.	32017 597
Brand	MITUTOYO
Manufacturer Part Number	342-263-30
Display	Digital
Min./max. length measuring range	50-75 mm
Digit increment	0.001 mm
Measuring arrangement	Cone tip (SR0.3)
Material of measuring bolt	Carbide
IP protection class	IP 65
Data transmission type	DIGIMATIC
Spindle clamping	Yes
Digit height	7.5 mm
Functions	ABS function, Origin (Dimension preset), Automatic switch-off
Min./max. measurement force	3-8 N
Angle of the tip	30 Degree
Error limit	2 µm
Number of rechargeable batteries/batteries	1 PCS
Battery designation	1,5 V SR44
DIN	863
Bracket depth	60 mm
Measuring spindle increments	0.5 mm
Calibration Group	D
Gross Weight	1.290 kg
Product Group	3MA

EAN

4946368689104