

SuperSchlag PLUS Betonbohrer

SuperSchlag PLUS Masonry Drill Bit

57500

Art.-Gruppe 56
Article Group 56**Der superelastische, bohrhammerfeste Stein- und Betonbohrer**

- ▶ Die spannungsarme Hoch-Temperatur-Kupferlötung der weitgehend volleingebetteten Hartmetallplatte sorgt für eine lange Lebensdauer und hält höchsten Beanspruchungen stand
- ▶ Drei gefräste Spannflächen am Schaft für perfekten Sitz des Bohrers im Bohrfutter ohne Durchrutschen (bis Länge 200 mm)
- ▶ Zur Verwendung in starken Schlagbohrmaschinen und leichten Bohrhämmern (bis max. 2 Joule Schlagenergie) mit 3-Backen-Bohrfutter sowie in Akku-Schlagbohrmaschinen
- ▶ Für Beton, Mauerwerk, Naturstein, Kunststein

The superelastic, drill hammer solid Stone and Masonry Drill Bit

- ▶ The low-stress high-temperature copper soldering of the almost fully embedded carbide plate ensures a long lifetime and maintains maximum work loads
- ▶ Three milled clamping surfaces on the shank for a perfect fit of the drill in the chuck without slipping (till length 200 mm)
- ▶ For use in heavy-duty hammer drills and light weight rotary hammers (with max. 2 joule impact energy) with 3 jaw chucks and also in cordless hammer drills
- ▶ Designed to drill: Concrete, Masonry, Natural and Artificial Stone

57500 Einzeln mit Aufhänger

575001 Quadro-Pack, je 10 Stück bis Ø 10 mm
je 5 Stück Ø 12 mm

57500 Single Packaging with Hanger

575001 X-Pack, with 10 pcs. up to Ø 10 mm,
with 5 pcs. Ø 12 mm**Einzeln mit Aufhänger/
Single Packaging with Hanger**

Ø mm	L	L2	Art.-Nr. Art.-No.
3,0	70	40	¹⁾ 57 503
4,0	85	50	57 504
5,0	85	50	57 505
5,0	150	115	57 505 150
6,0	100	60	57 506
6,0	150	110	57 506 150
6,5	100	60	575 065 *
6,5	150	110	575 065 150 *
7,0	100	60	57 507
7,0	150	110	57 507 150 *
8,0	120	80	57 508
8,0	200	160	57 508 200
8,0	400	360	57 508 400

**Einzeln mit Aufhänger/
Single Packaging with Hanger**

Ø mm	L	L2	Art.-Nr. Art.-No.
9,0	120	80	57 509 *
10,0	120	80	57 510
10,0	200	160	57 510 200
10,0	400	360	57 510 400
12,0	150	110	57 512
12,0	200	160	57 512 200
12,0	400	360	57 512 400
13,0	150	110	57 513
14,0	150	110	57 514
14,0	600	560	²⁾ 57 514 600 *
16,0	150	110	57 516
16,0	600	560	²⁾ 57 516 600
20,0	600	560	²⁾ 57 520 600 *

575001**Quadro-Pack mit Aufhänger/
X-Pack with Hanger**

Ø mm	L	L2	Art.-Nr. Art.-No.
4,0	85	50	575 041
5,0	85	50	575 051
6,0	100	60	575 061
8,0	120	80	575 081
10,0	120	80	575 101
12,0	150	90	575 121

1) mit Standard-Hartmetallplatte
with standard carbide tip**2) mit Mehrkant-Schaft**
with a multi-flat shank**3) nicht mehr lieferbar**
out of stock

* Lieferung nur solange der Vorrat reicht / Delivery while stocks last