

Specification of FBH300-2.5 Battery

REV: A

DATE: 2016/05/16

Description :	For FBH300-2.5	
Battery Type :	HR-3U	
Nominal Voltage :	3.6V	
Nominal Capacity :	2500mAh	
Charging Voltage :	6.0V	
Charging Current Range :	0.1C ~1C (Recommended)	
Discharging Current Range :	0.2C ~1C (Recommended)	
End Voltage of Discharge :	3.0V	
Temperature : (Recommended)	Charge :	± 0 ~ + 45°C (+ 32 ~ + 113°F)
	Discharge :	- 30 ~ + 60°C (- 22 ~ + 140°F)
	Storage :	- 20 ~ + 40°C (- 4 ~ + 104°F)
Overcharge detection voltage	N/A	
Overdischarge detection voltage	N/A	
Short protection function	N/A	
0V battery charging function	N/A	