

For inserts and modules of the EPIC® rectangular connectors

### Product Description



### Article List

| Part number | Article          | Version | Conductor cross-section (mm <sup>2</sup> ) | Cross-section ratio | Surface | Stripping length (mm) | Pieces / PU |
|-------------|------------------|---------|--|---------------------|---------|-----------------------|-------------|
| Contacts    |                  |         |  |                     |         |                       |             |
| 13162000    | H-D 1.6 machined | male    | 0,14 - 0,37                                | 1                   | Ag      | 8.0                   | 100         |
| 13163000    | H-D 1.6 machined | female  | 0,14 - 0,37                                | 1                   | Ag      | 8.0                   | 100         |
| 13162100    | H-D 1.6 machined | male    | 0,5  | 2                   | Ag      | 8.0                   | 100         |
| 13163100    | H-D 1.6 machined | female  | 0,5  | 2                   | Ag      | 8.0                   | 100         |

|          |                     |        |             |   |    |     |     |
|----------|---------------------|--------|-------------|---|----|-----|-----|
| 13162200 | H-D 1.6<br>machined | male   | 0,75 - 1    | 3 | Ag | 8.0 | 100 |
| 13163200 | H-D 1.6<br>machined | female | 0,75 - 1    | 3 | Ag | 8.0 | 100 |
| 13162300 | H-D 1.6<br>machined | male   | 1,5         | 4 | Ag | 8.0 | 100 |
| 13163300 | H-D 1.6<br>machined | female | 1,5         | 4 | Ag | 8.0 | 100 |
| 13162400 | H-D 1.6<br>machined | male   | 2,5         | 5 | Ag | 5.8 | 100 |
| 13163400 | H-D 1.6<br>machined | female | 2,5         | 5 | Ag | 5.8 | 100 |
| 13162500 | H-D 1.6<br>machined | male   | 0,14 - 0,37 | 1 | Au | 8.0 | 100 |
| 13163500 | H-D 1.6<br>machined | female | 0,14 - 0,37 | 1 | Au | 8.0 | 100 |
| 13162600 | H-D 1.6<br>machined | male   | 0,5         | 2 | Au | 8.0 | 100 |
| 13163600 | H-D 1.6<br>machined | female | 0,5         | 2 | Au | 8.0 | 100 |
| 13162700 | H-D 1.6<br>machined | male   | 0,75 - 1    | 3 | Au | 8.0 | 100 |
| 13163700 | H-D 1.6<br>machined | female | 0,75 - 1    | 3 | Au | 8.0 | 100 |
| 13162800 | H-D 1.6<br>machined | male   | 1,5         | 4 | Au | 8.0 | 100 |
| 13163800 | H-D 1.6<br>machined | female | 1,5         | 4 | Au | 8.0 | 100 |
| 13162900 | H-D 1.6<br>machined | male   | 2,5         | 5 | Au | 5.8 | 100 |
| 13163900 | H-D 1.6<br>machined | female | 2,5         | 5 | Au | 5.8 | 100 |

**Footnote:**

Photographs are not to scale and do not represent detailed images of the respective products.