

**Push switches**

<b>Order code</b>	<b>Manufacturer code</b>	<b>Description</b>
78-1708	MP0037	MP0037 VANDAL RESIST SWITCH SPNO (RC)

Push switches	Page 1 of 2
The enclosed information is believed to be correct, Information may change without notice due to product improvement. Users should ensure that the product is suitable for their use. E. & O. E.	Revision A 20/02/2007

## Vandal Resistant Switch SPNO

### Bulgin – MP0037

#### Specifications

Bulgin List No:	MP0037
Terminations:	Screw terminals
Switching:	S.P. Push to make Slow momentary action
Current Rating:	1A max.
Voltage Rating:	50V AC
Contact Resistance:	<10mΩ
Insulation Resistance:	>10 <sup>5</sup> MΩ
Dielectric Strength:	>1.0kV AC
Operating Temp. Range:	-20°C to +70°C
Sealing (Front panel only):	Protection Classification: IP66 EN60529 1992 (Terminals not sealed)
Materials:	
Mouldings:	Glass Filled Nylon
Switch Body:	Stainless Steel
Button:	Stainless Steel
Tags/Terminals:	Brass, Silver plated
Contacts:	Brass, Silver Plated, Silver
Max. Panel Thickness:	4.0mm
Mounting Hole:	19.0mm ±0.10mm

