



IWLAN RCOAX N-CONNECT FEMALE N-CONNECTOR 2.4 AND 5 GHZ CAN BE PRE-ASSEMBLED IN THE FIELD COAXIAL CABLE TAP FOR CONNECTING THE RCOAX CABLE TO FURTHER COMPONENTS

Electrical data

Number of electrical connections	1
Type of electrical connection	N-Connect female
Transmission frequency	0 ... 6 GHz
Impedance	50 Ω

Permitted ambient conditions

Ambient temperature	
<ul style="list-style-type: none"> during operation during storage during transport 	<p>-40 ... +85 °C</p> <p>-40 ... +85 °C</p> <p>-40 ... +85 °C</p>
Protection class IP	IP67

Design, dimensions and weight

Diameter	27 mm
Length	65 mm
Net weight	159 g

Standards, specifications, approvals

Certificate of suitability	
<ul style="list-style-type: none"> RoHS conformity 	Yes

Further Information / Internet Links

Internet-Link	
<ul style="list-style-type: none"> to website: Selector SIMATIC NET SELECTION TOOL to website: Industrial communication 	<p>http://www.siemens.com/snst</p> <p>http://www.siemens.com/simatic-net</p>

- to website: Industry Mall
- to website: Information and Download Center
- to website: Image database
- to website: CAx Download Manager
- to website: Industry Online Support

<https://mall.industry.siemens.com>

<http://www.siemens.com/automation/net/catalog>

<http://automation.siemens.com/bilddb>

<http://www.siemens.com/cax>

<https://support.industry.siemens.com>

last modified:

09.03.2015