

## Coaxial Cable Connector 11\_SMA-50-3-236/133\_N

### Description

Straight cable plug

Interface standards

IEC 60169-15\_MIL-STD-348A/310\_CECC 22110



### Technical Data

#### Electrical Data

Impedance	50 Ω		
Interface frequency max.	18 GHz		
Frequency range	DC to 1 GHz	1 to 2.5 GHz	2.5 to 5 GHz
Return loss	34 dB	32 dB	27 dB

#### Mechanical Data

Centre contact	soldered
Outer 2contact	crimped
Weight	0.003 kg

#### Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS)	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	SUCOPRO Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PTFE (Polytetrafluoroethylene)	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	
Crimp ferrule	Copper	

### Related Documents

Outline drawing	DOU-00169128
Catalogue drawing	DCA-00176231
Assembly instruction	DOC-0000349507

### Ordering Information

Bulk 500 pcs package	11_SMA-50-3-236/133_NP
Single package	11_SMA-50-3-236/133_NE

### Additional Information

Suitable cables	ENVIROFLEX_400, G_03262_D, RADOX_RF_400
-----------------	---