


Item code

CDSHM 18



Brief description:

male insert, 18 poles, Spring connection contacts SQUICH, 10A, 400V, silver plated, size "57.27", CLASS inserts

| Product description | |
|--|---|
| Model | male insert |
| Version | Spring connection contacts SQUICH |
| Series | CDSH |
| Product type | with male contacts |
| Family | CLASS inserts |
| Size | size "57.27" |
| N° of poles | 18 poles +  |
| Technical data | |
| Current | 10 A (A.C. and D.C.) |
| Voltage | 400 V |
| Sustained impulse voltage | 6kV |
| Pollution degree | 3 |
| Wire section | 0,14 mm ² - 2,50 mm ² |
| AWG size | 26 - 14 |
| Operating temperature range (min, max) | -40°C ... +125°C |
| Contact type | silver plated |
| Plugging cycles | ≥ 500 |
| IP degree of protection | IP20 without enclosure; IP65/IP66/IP67/IP68 with enclosure |
| Wire cross section PE | 0,14 - 4 mm ² ; AWG 20 - 12 |
| Other technical details | |
| Insulation resistance | ≥ 10 GΩ |
| Rated voltage according to UL/CSA | |
| Weight | 36,00 g |

| Approvals / Standards | |
|------------------------------|----------------------|
| Reference standard | EN 61984 (2001-11) |
| General ordering information | |
| EAN code | 8015747222617 |
| Tariff number | 85369095 |
| Packaging Information | |
| Packaging length | 245,00 mm |
| Packaging height | 165,00 mm |
| Packaging width | 215,00 mm |
| Packaging weight | 1,08 kg |
| Packaging volume | 8,69 dm ³ |
| Packaging description | Carton box |
| Packaging quantity | 30 Pcs |
| Packaging EAN code | 8015747222778 |
| Sub-packaging length | 197,00 mm |
| Sub-packaging height | 55,00 mm |
| Sub-packaging width | 113,00 mm |
| Sub-packaging weight | 0,18 kg |
| Sub-packaging volume | 1,22 dm ³ |
| Sub-packaging description | Carton |
| Sub-packaging quantity | 5 Pcs |
| Sub-packaging EAN barcode | 8015747222785 |



Item code

CDSHM 18



Notes

actuator button connections



Reopening