ZB4BD922

Potentiometer head, metal, black, Ø22, for use with Ø 6.35 mm shaft





Main

| Mairi | |
|-------------------------------|--|
| Range of product | Harmony XB4 |
| Product or component type | Head + mounting base for potentiometer |
| Device short name | ZB4 |
| Bezel material | Chromium plated metal |
| Mounting diameter | 0.87 in (22 mm) |
| Product compatibility | For use with Ø 6.35 mm shaft |
| Sale per indivisible quantity | 1 |
| Head type | Standard |
| | |

Complementary

| Net Weight | 0.18 lb(US) (0.08 kg) |
|------------------------------------|---------------------------------------|
| Resistance to high pressure washer | 7000000 Pa at 55 °C, distance : 0.1 m |
| Shape of signaling unit head | Round |
| Operator profile | Knurled knob, with white) |
| Device presentation | Basic element |

Environment

| Environment | |
|---------------------------------------|---|
| Protective treatment | TH |
| Ambient air temperature for storage | -40158 °F (-4070 °C) |
| Ambient air temperature for operation | -40158 °F (-4070 °C) |
| Electrical shock protection class | Class I IEC 60536 |
| IP degree of protection | IP66 conforming to IEC 60529 |
| NEMA degree of protection | NEMA 13 NEMA 4X |
| IK degree of protection | IK03 conforming to IEC 50102 |
| Standards | EN/IEC 60947-5-4 UL 508 JIS C8201-5-1 EN/IEC 60947-5-1 EN/IEC 60947-5-5 EN/IEC 60947-1 CSA C22.2 No 14 JIS C8201-1 |
| Product certifications | DNV CSA RINA LROS (Lloyds register of shipping) GL UL Listed BV |
| Vibration resistance | 5 gn (f= 2500 Hz) conforming to IEC 60068-2-6 |
| Shock resistance | 30 gn (duration = 18 ms) for half sine wave acceleration conforming to IEC 60068-2-27 50 gn (duration = 11 ms) for half sine wave acceleration conforming to IEC 60068-2-27 |

Ordering and shipping details

| Category | 22468 - PUSHBUTTONS,22MM(METAL) NEW |
|-----------------------|-------------------------------------|
| Discount Schedule | CS2 |
| GTIN | 00785901354604 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 0.17 lb(US) (0.08 kg) |
| Returnability | Yes |
| Country of origin | FR |

Packing Units

| Unit Type of Package 1 | PCE | |
|------------------------|------------------|--|
| Package 1 Height | 2.20 in (5.6 cm) | |
| Package 1 width | 1.73 in (4.4 cm) | |
| Package 1 Length | 2.05 in (5.2 cm) | |

Offer Sustainability

| Office Oddital lability | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| REACh Regulation | ☑ REACh Declaration |
| REACh free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | ₫Yes |
| China RoHS Regulation | [™] China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End Of Life Information |


Contractual warranty

| Warranty 18 months | |
|--------------------|--|
|--------------------|--|

Product data sheet Dimensions Drawings

ZB4BD922


Dimensions



- e: panel thickness: 1 to 6 mm / 0.04 to 0.24 in.
- (1) Potentiometer not included

ZB4BD922

Panel Cut-out for Pushbuttons, Switches and Pilot Lights (Finished Holes, Ready for Installation)



- (1) Diameter on finished panel or support
- (2) 40 mm min. / 1.57 in. min.
- (3) 30 mm min. / 1.18 in. min.
- (4) \emptyset 22.5 mm / 0.89 in. recommended (\emptyset 22.3 mm $_0$ ^{+0.4} / 0.88 in. $_0$ ^{+0.016})
- (5) 45 mm min. / 1.78 in. min.
- (6) 32 mm min. / 1.26 in. min.