

Clamps

With magnetic base



Version:

- Heat-treated steel
- Painted
- With self-locking trapezoid spindle and end safety device
- With flat support
- Centring hole Ø12 mm

Advantage:

- Durable and precise positioning of workpiece thanks to permanent magnet in the base.

Art. no.	26157 120
Min./max. support plate height	52-62 mm
Diameter	50 mm
Head diameter	50 mm
Diameter 2	50 mm
Max. force range	100 kN
Centring diameter	12 mm

EAN-Code

4020772073329

