

## Clamps

With magnetic base



### Execution:

- Heat-treated steel
- Painted
- With self-locking trapezoid spindle and end safety device
- With flat support
- Centring hole Ø12 mm

### Advantage:

- Durable and precise positioning of workpiece thanks to permanent magnet in the base.

<b>Art. no.</b>	<b>26157 120</b>
<b>Brand</b>	AMF
<b>Manufacturer Part Number</b>	73320
<b>Min./max. support plate height</b>	52-62 mm
<b>Diameter</b>	50 mm
<b>Head diameter</b>	50 mm
<b>Diameter 2</b>	50 mm
<b>Max. force range</b>	100 kN
<b>Centring diameter</b>	12 mm
<b>Gross Weight</b>	0.693 kg
<b>Product Group</b>	260



### EAN

4020772073329

