

Precision pointer snap gauges

Marameter FS



Application:

For precise testing of cylindrical parts directly on the machine tool.

Execution:

- Carbide measuring faces
- Movable anvil spring-mounted on bottom
- Consistent, repeatable measuring force
- Forged steel bracket
- Both measuring probes made from stainless, hardened steel
- Adjustable centring stop

Delivery:

In wooden box, display unit not included



Art. no.	31938 150
Brand	MAHR
Manufacturer Part Number	4455004
Min./max. length measuring range	150-200 mm
Measuring surface diameter	20 mm
Measurement force	15 N
Shank diameter	8 mm
Spindle clamping	Yes
Gross Weight	4.200 kg
Product Group	305

EAN

4059192017859

