



		A (mm)	B (mm)
<b>E1.310.012</b>	Mac 0	79	13
<b>E1.311.012</b>	Mac 1	91	20
<b>E1.312.012</b>	Mac 2	113	21
<b>E1.313.012</b>	Mac 3	131	22
<b>E1.314.012</b>	Mac 4	154	24
<b>E1.315.012</b>	Mac 5	176	25

## F.O. Macintosh Spatel

- Laryngoskop Spatel mit auswechselbarem Lichtleiter
- hochwertige Konstruktion aus Edelstahl für hohe Lebensdauer
- 5.500 Fasern sorgen für maximale Lebensdauer und Beleuchtungsstärke
- optimale Ausleuchtung durch größtmöglichen Querschnitt (Durchmesser 4 mm)
- Beleuchtungsstärke mit 3.7 V LED: ca. 10.500 Lux
- Beleuchtungsstärke mit 2.5 V Xenon: ca. 4.500 Lux
- kompatibel mit allen Griffen nach ISO 7376 (Grüner Standard)
- autoklavierbar bis 134°C – ca. 4.000 Zyklen
- Data-Matrix mit den wichtigsten Informationen



## F.O. Macintosh Blade

- laryngoscope blade with replaceable light guide
- high-quality stainless steel construction for a long service life
- 5.500 fibres to achieve the maximum service life and illumination
- optimal light emission due to the largest possible cross section (diameter: 4 mm)
- brightness approx. 10.500 Lux at 3.7 V LED
- brightness approx. 4.500 Lux at 2.5 V Xenon
- compatible with all handles according to ISO 7376 (green standard)
- autoclavable up to 134° C – approx. 4.000 times
- Data-Matrix with most important information

