

# PRODUCT SPECIFICATION

**Carl  
Kammerling**  
International

<b>Brand</b>	C.K
<b>Product Range</b>	PVC pipe cutters
<b>Catalogue number</b>	2238, 2239 & 2240
<b>Date</b>	14/05/2014

## Range Description

Ratchet PVC Pipe cutters

## Features

430001

- Glass fibre reinforced body – strong and lightweight
- Ergonomic handle design for increased leverage
- Razor sharp stainless steel blade for corrosion protection and performance

## Features

430003

- Heavy duty cast Aluminium body for strength
- Ratchet cutting mechanism for effortless clean cuts
- Razor sharp stainless steel blade for corrosion protection and performance
- Cable trunking adaptor included for convenience
- Cuts a wide variety of plastic and rubber products



430001



*With trunking adaptor*

430003

**Features**

T2240

- Aluminium Anvils and handles – lightweight and comfortable
- Razor sharp stainless steel blade for corrosion protection and performance
- Supplied with 5 different anvils: general purpose anvil, 90 degree square anvil, multi angle anvil, 25mm single radius anvil and double radius anvil
- Quick and easy anvil hanging – for convenience and speed



T2240

Item Number	Item Description	EAN No	Commodity code	Carton Qty
430001	PVC conduit pipe cutter	5051074300010	82034000	3
430003	Ratchet conduit cutter	5051074300034	82034000	3
T2240	Multi cutter	5013969062847	82034000	3

**Technical product information**

**430001**

Body – Glass fibre reinforced plastic  
Blade – Stainless steel

Capacities:  
Cuts up to 28mm diameter (1 1/4")

Suitable for cutting PVC conduit, Blue water mains plastic pipe, rubber/plastic hose, Pneumatic pipes, electrical sleeving etc.

**430003**
















Body – Die cast Aluminium  
Blade – Stainless steel

Capacities:  
Cuts up to 32mm diameter (1 1/4") PVC pipe/conduit  
Can also be used to cut plastic water pipe, hose pipe, electrical sleeving, cable trunking, etc.

**T2240**

Body – Die cast Aluminium  
Blade – Stainless steel

Capacities

	<table border="1"> <tr> <td>For PVC Pipe &amp; Hose Jaw anvil of 17mm &amp; 20mm</td> <td></td> <td>Max capacity 3mm</td> </tr> <tr> <td>90° Square anvil</td> <td></td> <td>Max capacity 2mm</td> </tr> <tr> <td>Flat anvil General flat material cutting</td> <td></td> <td>For laminated soft wood less than 10mm Also will cut 2mm thick square section trunking up to 35mm wide</td> </tr> <tr> <td>Multi-angle anvil Cutting for 45°, 75°, 90°, 105°, 120° angles</td> <td></td> <td>For laminated soft wood less than 10mm</td> </tr> <tr> <td>For PVC Pipe &amp; Hose Jaw anvil of 27mm dia.</td> <td></td> <td>Max capacity 3mm</td> </tr> </table>	For PVC Pipe & Hose Jaw anvil of 17mm & 20mm		Max capacity 3mm	90° Square anvil		Max capacity 2mm	Flat anvil General flat material cutting		For laminated soft wood less than 10mm Also will cut 2mm thick square section trunking up to 35mm wide	Multi-angle anvil Cutting for 45°, 75°, 90°, 105°, 120° angles		For laminated soft wood less than 10mm	For PVC Pipe & Hose Jaw anvil of 27mm dia.		Max capacity 3mm
For PVC Pipe & Hose Jaw anvil of 17mm & 20mm		Max capacity 3mm														
90° Square anvil		Max capacity 2mm														
Flat anvil General flat material cutting		For laminated soft wood less than 10mm Also will cut 2mm thick square section trunking up to 35mm wide														
Multi-angle anvil Cutting for 45°, 75°, 90°, 105°, 120° angles		For laminated soft wood less than 10mm														
For PVC Pipe & Hose Jaw anvil of 27mm dia.		Max capacity 3mm														
	<p>Can be used to cut plastic trim, conduit, trunking, hose, PVC pipe, wooden dowel etc.</p> <p><b>Note</b> These products are not designed to cut wire, metal or reinforced tubing – attempting to cut such materials will damage the blade</p>															
Standards compliance	None applicable															
User health and safety information	None applicable															
RoHS/WEEE compliance	This product range does not fall within the scope of RoHS or WEEE regulations															
Material safety data	None applicable															
Warranty	C.K cutters are guaranteed for life against imperfect materials or workmanship The cutter working mechanism and the cutting edge of the blade will wear over time, this is not covered under the terms of the warranty															
Country of origin	Taiwan															

## Dimensional details

Item	Product only				Product on primary packaging			
	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
430001	72	25	195	166	130	28	280	200
430003	94	30	205	360	130	35	280	410
T2240	80	25	210	461	230	40	295	559

Item	Shelf box (secondary packaging)				Euro Pallet data Wi x Hi	
	Width mm	Depth mm	Height mm	Gross weight g	No of cartons on base	Number of rows high
430001	227	295	57	717		
430003	290	370	37	1365		
T2240	235	305	80	1882		

## Packaging waste details

Item	Primary Packaging				Secondary packaging			
	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
430001	16	Blister	18	Backing card			117	Box
430003	22	Blister	28	Backing card			135	Box
T2240	85	Blister	13	Backing card			205	Box