





REV	DATE	DESCRIPTION
NC	07/23/04	INITIAL RELEASE



- NOTES:  
 1. CRIMPED FERRULE HEX SIZE 213\*  
 2. SOLDER CENTER CONTACT.

RECOMMENDED CABLE STRIPPING DIM'S  
 FOR 8 GHz PERFORMANCE CABLE WITH -OIL BRND.  
 ELECTRICAL:  
 A) IMPEDANCE: 50ohms  
 B) FREQUENCY RANGE: DC-6 GHz  
 C) VSWR (RETURN LOSS): 1.4 (13.5dB), MAX.  
 D) DIELECTRIC WITHSTANDING VOLTAGE:  
 1500 VRMS, MIN.

QTY	DESCRIPTION	MATERIAL	FINISH	DO NOT SCALE DRAWING	APPROVALS	DATE	REV	DATE	DESCRIPTION
1	CRIMPED FERRULE	BRASS	NICKEL			07/23/04	NC	07/23/04	INITIAL RELEASE
1	CONTACT PIN	COPPER	NICKEL						
1	INSULATOR	PHOS. BRONZE	GOLD						
1	BODY	TITANIUM	NATURAL						
1	HEX NUT	BRASS	NICKEL						
1	CONTACT PIN	COPPER	NICKEL						
1	INSULATOR	PHOS. BRONZE	GOLD						
1	BODY	TITANIUM	NATURAL						

**Amphenol Connex**

PART DESCRIPTION  
 TNC REVERSE POLARITY R/A CRIMP PLUG  
 (FOR RG-58/U, 58C/U CABLE)

PART NO. 122140RP

DWG NO. 122140RP.DWG

REV. NC

SIZE A

SCALE NA