

U.I. Lapp GmbH	<b>DATASHEET</b>	
	<b>SKINDICHT® SHZ-M</b>	<b>52106785</b> <b>14.11.2013</b>

With incised sealing ring for adjustment to several cable diameters  
 High strain relief  
 Robust  
 For cables with large outer diameters



Mechanical resistance



Optimum strain relief

### Application range

Compact brass cable gland for reliable strain relief, solid, for large cable diameters.

### Design

Metric connection thread acc. to EN 50262

### Note

SKINDICHT® SHZ-M-XL is similar to the SKINDICHT® SHZ-M, but has an extended connection thread for thick walls

Counter nut to be used: SKINDICHT® SM-M

Example description: SHZ-M 16/916 = metric connection thread 9 = PG function thread

### Remark

Photographs are not to scale and do not represent detailed images of the respective products.


### Technical Data

Article designation / size:	50 x 1,5
Ø-F mm:	35 - 43
Max. fitting size for installation (mm):	78
Function thread PG:	42
SW1/SW2 mm:	57 / 57
Overall length, C (mm):	70
Thread length, D (mm):	14
Pieces / PU:	5
Caution:	The installation dimensions can be found in appendix T21
Material:	Body: nickel-plated brass Sealing ring: CR/NBR O-ring: NBR
Protection rating:	IP 55
Temperature range:	-20°C to +80°C



Product Management	Document: SKINDICHT® SHZ-M	1 / 2
--------------------	----------------------------	-------

U.I. Lapp GmbH	<b>DATASHEET</b>	 <b>LAPP GROUP</b>
	<b>SKINDICHT® SHZ-M</b>	52106785 14.11.2013



Product Management	Document: SKINDICHT® SHZ-M	2 / 2
--------------------	----------------------------	-------