

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0923151424](#)  
**Status:** **Active**  
**Overview:** [Picoflex Ribbon-Cable Connectors](#)  
**Description:** Picoflex PF-50 IDT-to-Picoflex PF-50 IDT Off-the-Shelf (OTS) Cable Assembly, 240.00mm Length, Tin (Sn) Plating, 14 Circuits

**Documents:**

<a href="#">3D Model</a>	<a href="#">Datasheet (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Product Specification PS-99020-0011-001 (PDF)</a>	

**Application tooling part link**

Application Tooling Part Link	62100-6000
Application Tooling Part Link	62100-6010

**General**

Product Family	Cable Assemblies
Series	<a href="#">92315</a>
Assembly Configuration	Dual Ended Connectors
Connector to Connector	Picoflex IDT-to-IDT
Overview	<a href="#">Picoflex Ribbon-Cable Connectors</a>
Product Name	Picoflex
Type	Ribbon Cable Assembly
UPC	193264715206

**Physical**

Cable Length	240.00mm
Circuits (Loaded)	14
Gender	Female-Female
Lock to Mating Part	None
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Polyester
Net Weight	1.912/g
Number of Rows	2
Packaging Type	Bag
Pitch - Mating Interface	1.27mm
Plating min - Mating	2.032µm
Plating min - Termination	2.032µm
Single Ended	No
Termination Interface: Style	IDT or Pierce
Wire Size AWG	28
Wire/Cable Type	PVC, Ribbon Cable


**Electrical**

Current - Maximum per Contact	1.2A
Voltage - Maximum	250V

**Material Info**

**Reference - Drawing Numbers**

Product Specification	PS-99020-0011-001
Sales Drawing	SD-92315-001



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2020)4578-DC (25  
June 2020)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Not Reviewed

Not Relevant

Not Contained

**Search Parts in this Series**

[92315](#) Series

**Mates With**

Picoflex PF-50 Header<br>[90325](#) , [90800](#) ,  
[90779](#) , [90715](#) , [90814](#)

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

**Description**

**Product #**

Extractor Tool for Connectors	<a href="#">621006000</a>
-------------------------------	---------------------------

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**