

# 7.5mm 15A Standard Profile 90 Degree Terminal Blocks

Pitch: 7.5mm  
 Rated voltage/current: 300V/15A  
 Operation temperatures: -40°C to +105°C  
 Withstand voltage: 2000V AC for 60s  
 Insulation resistance: 500MΩ at 500V DC  
 Wire range: 24 to 12AWG 2.5mm<sup>2</sup>  
 Max. torque value: 0.4 Nm



Housing: PA66 (UL 94V-0)  
 Housing colour: Green  
 Screw: M2.5, Zinc-plated steel (A3)  
 Wire cage: Nickel-plated brass  
 Pin header: Tin-plated brass  
 Wire stripping length: 6 to 7mm  
 Wave soldering: 260°C for 5s  
 Hand soldering: 350°C for 10s

Order code	Poles
<b>21-3960</b>	2
<b>21-3961</b>	3

