

MPR67 REPEATER PROFIBUS DP 2 SEGMENTS


Upto 12 Mbit/s, IP67

Repeater PROFIBUS DP + PROFIsafe
2 segments
Protection IP67

Housing fully potted. For connection cables please see chapter "Connection Technology"

[Link to Product](#)

Illustration



Product may differ from Image

Approvals



Technical Data

Operating voltage	24 V DC (EN 61131-2)
Module Supply	via PIN 4 sensor supply (7/8" power)
Current consumption	approx. 80 mA
Transfer rate	to 12 Mbit/s

General data

The information in this brochure has been compiled with the utmost care.

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 05/15

Murrelektronik GmbH | Falkenstraße 3, 71570 Oppenweiler | Fon +49 (71 91) 47-0, Fax +49 (71 91) 47-491000 | shop@murrelektronik.de | shop.murrelektronik.de

Protection	IP67
Mounting method	2-hole screw mounting
Temperature range	0...+55 °C (storage temperature -20...+75 °C)
Dimensions H × W × D	151×30×34.5 mm

Diagnostic

Communication status	via LED
----------------------	---------

Commercial data

country of origin	DE
customs tariff number	85176200
minimum order quantity	1