Banana Plugs (Only for Safety Extra-Low Voltage)

For sockets Ø 4 mm / 0.157 in 0.08 - 2.5 mm² 42 V 20 A AWG 28 - 14

0.08 - 2.5 mm² 42 V 20 A

For sockets Ø 4 mm / 0.157 in AWG 28 - 14

For sockets Ø 4 mm / 0.157 in AWG 28 - 14

0.08 - 2.5 mm² 42 V 20 A 9 – 11 mm / 0.39 in

9 – 11 mm / 0.39 in

9 – 11 mm / 0.39 in







Color	Item No.	Pack. unit pcs	Color	ltem No.	Pack. unit pcs		ltem No.	Pack. unit pcs
Banana plug, for sockets Ø 4 mm/0.157 in			Banana plug, for sockets Ø 4 mm/0.157 in			Banana plugs, for sockets Ø 4 mm/0.157 in		
orange	215-211	50	yellow	215-511	50	color mixed	215-111	50
						10 each – orange, white, black, blue, yellow		





Color	ltem	Pack. unit	Color	ltem	Pack. unit	
	No.	pcs		No.	pcs	
Banana plu	Banana plug, for sockets Ø 4 mm/0.157 in			Banana plug, for sockets Ø 4 mm/0.157 in		
red	215-212	50	blue	215-711	50	




To connect: Press button fully and insert stripped conductor into square entry hole and release.





Color	Item No.	Pack. unit	Color	ltem No.	Pack. unit
Banana plug, for sockets Ø 4 mm/0.157 in			Banana plug, for sockets Ø 4 mm/0.157 in		
black	215-311	50	arev	215-811	50



Banana plug used as test plug Picture shows test adapter 209-170





Color	Item No.	Pack. unit pcs	Color	ltem No.	Pack. unit pcs	
Banana plug, for sockets Ø 4 mm/0.157 in			Banana plug, for sockets Ø 4 mm/0.157 in			
green	215-411	50	green-yellow	215-911	50	
white	215-611	50				

