

Slides DS 5321, width 19.1 mm, up to 180 kg, Over-Extension

Material:

Stainless steel 1.4301 (AISI 304).




Telescopic precision ball bearing slides for applications in the industrial and electronics sector.

- Hold-in in the closed position.
- Mounting bracket for electronic cabinets on request.
- Service life 10,000 / 80,000 cycles.
- Temperature range: -20°C to +70°C.



Accuride

Ordering Details: e.g.: Product No. 649 440 30, Slides DS 5321



Product No. per Pair DS 5321	Slide Length mm	Travel +/-3,2 mm	A mm	B mm	C mm	D mm	E mm	F mm	Load Rating ¹⁾ per pair kg	Weight per pair kg
649 440 30	300	323,5	-	-	192	224	-	-	140 / 120	1,66
649 440 35	350	373,5	-	-	224	256	-	-	150 / 130	1,95
649 440 40	400	423,5	160	192	288	320	128	160	160 / 140	2,25
649 440 45	450	473,5	160	192	320	352	128	160	170 / 150	2,56
649 440 50	500	523,5	192	224	384	416	160	192	180 / 160	2,82
649 440 55	550	573,5	192	224	416	448	160	192	170 / 150	3,12
649 440 60	600	623,5	256	288	480	512	192	256	160 / 130	3,41
649 440 70	700	723,5	288	320	576	608	256	288	130 / 110	4,03
649 440 80	790	803,5	352	384	672	704	320	352	100 / 100	4,52

¹⁾ At 10,000 / 80,000 cycles.

Note

Recommended mount: M5 countersunk / 6mm countersunk euro screw.

Use all mounting positions to achieve the max. load rating.

Attention: Vertical mounting only.