

Product data sheet

Item No. 94.425.2000.7

Cable assembly BST14I2KFBS 50 20GN01

geis® Extension cable female - male; length: 2m; type BST14I2;  
2-pole;50 V / 3 A; colour of coding: grün with black strain-relief;  
cable: FB-2Y(ST)Y2x2x0,8, colour: grün



Item No.	94.425.2000.7
EAN	4015573459861
Order Unit	50 Piece(s)

Certificates / Approvals



Technical data

**General**

Rated current	3 A
Rated voltage	50 V
Rated impulse voltage	0.8 kV
Pollution degree	2
Mechanical coding	Yes
Interlockable	No
Color of coding/ contact carrier	Green
Marking of poles	
Color of housing inclusive strain relief	Black

**Model**

Number of poles	2
Nominal cross section conductor	0.5 mm <sup>2</sup>
Degree of protection (IP)	IP20
Cable type	FB-2Y(ST)Y 2x2x0.8
Cable colour	Green
Cable diameter	6.1 mm
Version of cable	Female - male

**Material**

Surface finish	Gilt
Halogen free	No
Continuous temperature of cable	70 °C
Insulation components continuous temperature	100 °C

**Dimensions**

Total length	2 m
--------------	-----