

## heavy-duty cabinet with centre divider – load capacity 1200 kg

with 4 shelves, width 1485 mm



### Application:

For storing heavy and long materials, tools, stored goods, forming and stamping dies.

### Execution:

- extremely robust and solid welded sheet steel construction with reinforced mounting profiles
- sheet steel shelves, galvanised, height-adjustable in 30 mm grid
- reinforced hinged doors, door opening angle 270°
- lockable with cylinder lock and rotary bolt lock with 3-point latching

### Advantage:

- large storage space for bulky operational materials or heavy stored goods
- heavy parts are cleared and stored securely and conveniently
- extremely strong owing to high load capacity

### Delivery:

fully assembled including floor anchoring



<b>Art. no.</b>	<b>50147 046</b>
<b>Brand</b>	ANKE
<b>Door design</b>	Full-sheet panel
<b>Width</b>	1485 mm
<b>Depth</b>	630 mm
<b>Height</b>	1950 mm
<b>Number of shelves</b>	8
<b>Load-carrying capacity per shelf</b>	160 kg
<b>Load-carrying capacity</b>	1200 kg
<b>With partition wall</b>	Yes
<b>Central locking</b>	Yes
<b>Lock type</b>	Twist-grip lock with three-point fastening
<b>Material</b>	Sheet steel
<b>Cabinet colour</b>	Light grey RAL 7035
<b>Colour of front</b>	Anthracite grey RAL 7016
<b>Surface</b>	Powder-coated
<b>Gross Weight</b>	197.601 kg
<b>Product Group</b>	502

### EAN

4014641158354