


AL-23P (Artikel-Nr. 155060)

SPECIFICATIONS:

| TYPE | UNIT | AL-23P |
|-----------------------|--------------------|-----------------|
| Nominal Impedance | Ω | $8 \pm 20\%$ |
| Nominal Power | W | 0.1 |
| Maximum Power | W | 0.2 |
| Resonant Frequency | Hz | 1.500 ± 200 |
| Frequency Range | Hz | 1.200~6.500 |
| Sensitivity | dB | $>78 \pm 3$ |
| Operating Temperature | $^{\circ}\text{C}$ | -20~+60 |
| Storage Temperature | $^{\circ}\text{C}$ | -30~+70 |

DIMENSIONS :

(Unit: mm)



Frequency response :

