

**Cable glands  
VP 13,5-K54**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



For sealing surplus threaded holes to maintain the IP class of protection

**General ordering data**

Type	VP 13,5-K54
Order No.	<a href="#">0294960000</a>
Version	Cable glands, Blanking plug, Polyamid 6 (PA6 - GF30), RAL 7035, PG 13.5, IP 54
GTIN (EAN)	4008190152659
Qty.	100 pc(s).

# Datenblatt

## Cable glands VP 13,5-K54

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technische Daten

### Dimensions and weights

Length	10 mm	Net weight	1.8 g
--------	-------	------------	-------

### General information

Cable gland	PG	Colour code	RAL 7035
DIN	DIN 46320 (for PG thread)	External thread	PG 13.5
Head diameter	25 mm	Length of thread	5 mm
Material	Polyamid 6 (PA6 - GF30)	Operating temperature range, max.	100 °C
Operating temperature range, min.	-40 °C	Protection degree with GWDR	IP 65
UL 94 flammability rating	V-2		

### Classifications

ETIM 3.0	EC000032	UNSPSC	30-21-18-01
eClass 5.1	27-14-91-10	eClass 6.2	27-14-91-10
eClass 7.1	27-14-91-10		

### Product information

Descriptive text ordering data	Other versions available on request. The sealing plugs must be tightened "hand-tight" with the screwdriver.
Descriptive text technical data	Optional sealing ring

### Approvals

ROHS	Conform
------	---------