


THERMASGARD® TH

Immersion sleeves made of stainless steel or brass, nickel-plated, for temperature sensors and measuring transducers, series Thor 1 and form B



S+S REGELTECHNIK


Dimensional drawing TH-ms / xx



TH-ms / xx

Brass immersion sleeve
thread-sealing, conical, according to DIN 10226


Dimensional drawing TH-VA / xx



TH-VA / xx

Stainless steel immersion sleeve
flat-sealing, cylindrical, according to DIN 228

Dimensional drawing TH-VA / xx / 90



TH-VA / xx / 90

Stainless steel immersion sleeve with neck tube
flat-sealing, cylindrical, according to DIN 228

THERMASGARD® TH – Immersion sleeve Ø 8 mm					
Type / WG01	p _{max} (static)	T _{max}	Inserted length (EL)	Item No.	Price
TH-<u>ms</u> / xx	Brass nickel-plated			Ø 8 x 0.75 mm	
TH-MS 50MM	10 bar	+150 °C	50 mm	7100-0011-0010-001	7,69 €
TH-MS 100MM	10 bar	+150 °C	100 mm	7100-0011-0020-001	8,00 €
TH-MS 150MM	10 bar	+150 °C	150 mm	7100-0011-0030-001	8,84 €
TH-MS 200MM	10 bar	+150 °C	200 mm	7100-0011-0040-001	9,32 €
TH-MS 250MM	10 bar	+150 °C	250 mm	7100-0011-0050-001	9,63 €
TH-MS 300MM	10 bar	+150 °C	300 mm	7100-0011-0060-001	11,06 €
TH-MS 350MM	10 bar	+150 °C	350 mm	7100-0011-0070-001	13,05 €
TH-MS 400MM	10 bar	+150 °C	400 mm	7100-0011-0080-001	11,48 €
TH-<u>VA</u> / xx	Stainless steel VA 1.4571			Ø 8 x 0.75 mm	
TH-VA 50MM	40 bar	+600 °C	50 mm	7100-0012-0010-001	14,69 €
TH-VA 100MM	40 bar	+600 °C	100 mm	7100-0012-0020-001	15,47 €
TH-VA 150MM	40 bar	+600 °C	150 mm	7100-0012-0030-001	16,26 €
TH-VA 200MM	40 bar	+600 °C	200 mm	7100-0012-0040-001	17,37 €
TH-VA 250MM	40 bar	+600 °C	250 mm	7100-0012-0050-001	18,26 €
TH-VA 300MM	40 bar	+600 °C	300 mm	7100-0012-0060-001	22,74 €
TH-VA 350MM	40 bar	+600 °C	350 mm	7100-0012-0070-001	23,16 €
TH-VA 400MM	40 bar	+600 °C	400 mm	7100-0012-0080-001	23,63 €
TH-<u>VA</u> / xx / 90	Stainless steel VA 1.4571, incl. neck tube (90mm)			Ø 8 x 0.75 mm	
TH-VA 50/90MM	40 bar	+600 °C	50 mm	7100-0012-2010-001	22,11 €
TH-VA 100/90MM	40 bar	+600 °C	100 mm	7100-0012-2020-001	23,16 €
TH-VA 150/90MM	40 bar	+600 °C	150 mm	7100-0012-2030-001	24,36 €
TH-VA 200/90MM	40 bar	+600 °C	200 mm	7100-0012-2040-001	25,53 €
TH-VA 250/90MM	40 bar	+600 °C	250 mm	7100-0012-2050-001	26,79 €
TH-VA 300/90MM	40 bar	+600 °C	300 mm	7100-0012-2060-001	29,26 €
Note:	Inner diameter of socket 6.5 mm				