


E11764



Wirable socket

SDOAH030MSSFKPG




Application		
Special feature		Free from silicone; Gold-plated contacts
Free from silicone		yes
Electrical data		
Operating voltage	[V]	< 250 AC
Max. current load total	[A]	4; (...40 °C)
Operating conditions		
Ambient temperature	[°C]	-25...85
Protection		IP 67
Mechanical data		
Weight	[g]	27.8
Dimensions	[mm]	35 x 20 x 30
Materials		PA
Material nut		brass, nickel-plated
Remarks		
Pack quantity		1 pcs.
Electrical connection		
screw terminals: ...0.75 mm ² ; Cable sheath: Ø 4...6 mm		
Electrical connection - socket		
Connector: 1 x M12, angled; Moulded body: PA; Locking: brass, nickel-plated; Contacts: gold-plated		

E11764

Wirable socket

SDOAH030MSSFKPG



Connection

