


# TECHNICAL DATASHEET

Update : 25/02/2019

## INTERNAL BORING BAR 95° MWLNR/L - 06



### Characteristics

Ref.	EAN	Diameter mm	Head length mm	Type of assembly	Type of tool tip attachment	Min reaming diameter mm
832766	3660338054259	20	180	Right	A20Q MWLNR 06	25
832767	3660338054266	20	180	Left	A20Q MWLNL 06	25
832768	3660338054273	25	200	Right	A25R MWLNR 06	32
832769	3660338054280	25	200	Left	A25R MWLNL 06	32
832771	3660338054303	32	250	Left	A32S MWLNL 06	40
832770	3660338054297	32	250	Right	A32S MWLNR 06	40