

## Han-Eco 24B-HSE-for DL-M32-glanded



Part number	19 43 124 0527
Specification	Han-Eco 24B-HSE-for DL-M32-glanded
HARTING eCatalogue	<a href="https://b2b.harting.com/19431240527">https://b2b.harting.com/19431240527</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Eco® B
Type of hood/housing	Hoods
Description of hood/housing	With integrated cable gland

### Version

Locking type	Double locking lever
Size	24 B
Version	Side entry
Cable entry	1x M32

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Number of relockings	≥500
Degree of protection acc. to IEC 60529	IP66
Clamping range	13 ... 21 mm

### Material properties

Material (hood/housing)	Polyamide Fibre-glass reinforced
Colour (hood/housing)	RAL 9005 (jet black)
Material flammability class acc. to UL 94	V-0

### Specifications and approvals

Specifications	IEC 61984 EN 45545-2 R22: HL1, HL2, HL3 EN 45545-2 R23: HL1, HL2, HL3 EN 45545-2 R24: HL1, HL2, HL3
----------------	--



Pushing Performance

## Commercial data

Packaging size	1
Net weight	194.5 g
Country of origin	Germany
European customs tariff number	85389099