

# Wiha SoftFinish®.

The convenient expert for dry applications.



product  
design  
award

1997



*The right tool at a glance, thanks to the printed screw symbol on the handle end.*

The Wiha SoftFinish® zone features a solid moulded core with soft outer grip. This requires less force, yet achieves 40% more torque than conventional handles. The handle is shaped to fit comfortably in the hand, providing maximum through forces in dry working conditions.

If a stuck screw has to be loosened, a precise hammer blow can be applied to the solid steel cap. Due to the hex blade extending through the handle to the steel cap, there is no loss of impact energy.



*The solid steel cap at the end of the SoftFinish® handle enables controlled hammer blows, for example, when loosening a tight screw.*



*Due to the solid steel cap and hex blade extending through the handle, there is no loss of impact energy when a precise hammer blow is applied.*


*Blade with hex bolster for wrenches to use on particularly tight screws.*



## Wiha SoftFinish®.

- Multi-component SoftFinish® handle provides maximum user comfort
- Ergonomically perfect handle design
- Printed screw symbol on handle end for fast identification
- Available in versions with round blade, hex blade or hex blade with solid steel cap
- Blade made of high quality CVM-steel, through-hardened and chrome plated
- Wiha ChromTop®-finish on tip for a perfect fit every time

## For slotted screws.


**302** SoftFinish® slotted cabinet screwdriver.  
**Round blade.**

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.  
 Wiha ChromTop® finish on tip for a perfect fit every time.


Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.

Standards: DIN ISO 2380.

Application: Particularly suitable for dry applications.

Order-No.	⌀	↔	⊖	●	↔	↕	↔
00684	2.0*	65	0.4	2.0	169	23	10
00685	2.5	75	0.4	2.5	179	23	10
00686	3.0*	80	0.5	3.0	184	23	10
00687	3.0	100	0.5	3.0	204	23	10
00689	3.0*	150	0.5	3.0	254	23	10
00690	3.0*	200	0.5	3.0	304	23	10
32383	3.0	300	0.5	3.0	404	23	5
00691	3.5	100	0.6	3.5	204	23	10
26931	3.5*	200	0.6	3.5	304	23	10
00692	4.0	100	0.8	4.0	211	30	10
00694	4.0*	150	0.8	4.0	261	30	10
00695	4.0*	200	0.8	4.0	311	30	10
00696	4.0*	300	0.8	4.0	411	30	5
27753	4.5*	80	0.8	4.5	191	30	10
00697	4.5*	125	0.8	4.5	236	30	10
00698	5.5	125	1.0	5.5	236	30	10
00700	5.5	150	1.0	5.5	261	30	10
00701	5.5*	200	1.0	5.5	311	30	10
00702	5.5*	300	1.0	5.5	411	30	5
32384	6.0	300	1.0	6.0	418	36	5

\* Additional dimension. Non-DIN size.


**302** SoftFinish® slotted workshop screwdriver.  
**Round blade.**

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.  
 Wiha ChromTop® finish on tip for a perfect fit every time.

Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.

Standards: DIN ISO 2380.

Application: Particularly suitable for dry applications.

Order-No.	⌀	↔	⊖	●	↔	↕	↔
27754	6.0	100	1.0	5.5	218	36	10
27755	6.0	150	1.0	5.5	268	36	10
00704	6.5	100	1.2	6.0	218	36	10
00703	6.5	150	1.2	6.0	268	36	10
00706	6.5*	200	1.2	6.0	318	36	5
00708	8.0	150	1.2	7.0	274	41	10
00707	8.0	175	1.2	7.0	299	41	5
00709	8.0	175	1.6	7.0	299	41	5
32399	8.0	300	1.2	7.0	424	41	5
00711	10.0	200	1.6	8.0	324	41	5
32400	10.0	300	1.6	8.0	424	41	5
00712	12.0	250	2.0	8.0	374	41	5
00713	14.0	250	2.5	11.0	374	41	5

\* Additional dimension. Non-DIN size.

## For slotted screws.


**308** SoftFinish® slotted screwdriver.  
**Hex blade with hex bolster.**

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.  
 Wiha ChromTop® finish on tip for a perfect fit every time.

Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.

Standards: DIN 5265, ISO 2380.

Application: Particularly suitable for dry applications.

Order-No.	⌀	↔	⊖	●	⊖	↔	↕	↔
00731	3.5	75	0.6	4.0	-	186	30	10
00732	4.5*	90	0.8	4.0	-	201	30	10
00733	5.5	100	1.0	5.0	8	213	36	10
00734	6.5	125	1.2	6.0	10	238	36	10
00735	7.0*	125	1.1	6.0	10	238	36	10
00736	8.0	150	1.2	8.0	13	268	41	10
00737	9.0*	150	1.4	8.0	13	268	41	10
00738	10.0	175	1.6	8.0	13	293	41	5
00739	12.0	200	2.0	10.0	16	318	41	5
00740	14.0	250	2.5	10.0	16	368	41	5

\* Additional dimension. Non-DIN size.


**530** SoftFinish® slotted screwdriver.  
**Hex blade with hex bolster, solid steel cap.**

Order-No.	⌀	↔	⊖	●	⊖	↔	↕	↔
03223	3.5	75	0.6	4.0	-	186	30	10
03224	4.5*	90	0.8	4.0	-	201	30	10
03225	5.5	100	1.0	5.0	8	213	36	10
03226	6.5	125	1.2	6.0	10	238	36	10
03228	8.0	150	1.2	8.0	13	271	41	5
03230	10.0	175	1.6	8.0	13	296	41	5
03231	12.0	200	2.0	10.0	16	321	41	5
03232	14.0	250	2.5	10.0	16	371	41	5

\* Additional dimension. Non-DIN size.


**398** SoftFinish® slotted screw-holding screwdriver.  
**Clamping sleeve holds the screw.**

Blade: Chrome-vanadium steel, through hardened, black-finish.

Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.

Application: For setting and turning screws in difficult to access areas.

Order-No.	⌀	↔	⊖	↔	↕	↔
32867	2.5	75	0.4	186	30	5
32868	3.0	100	0.5	211	30	5
32869	4.0	125	0.8	243	36	5
32870	5.0	150	1.0	268	36	5
32871	6.0	175	1.2	293	36	5

Farnell Order Code	Wiha Order Number
830872	00698
830902	00708