

ToLEDo AVANT T8 CCG and AC

TOLEDO T8 V5 2FT 10W 1000LM 840
0028275



Product features

- Energy efficient and affordable LED T8 solution to replace conventional fluorescent T8 lamps
- Omnidirectional 320° uniform light distribution thanks to glass tube construction design, same as traditional fluorescent T8 tubes
- High lumen package - 1000lm
- High lumen efficacy - 100 lm/W
- Energy rating - A+
- Switching cycles - 200,000X
- Average life 40,000 hours lifespan (L70 F50)
- Wide beam angle - 220°
- High power factor - 0.90
- Suitable for general illumination in offices, supermarkets, department stores, train stations, petrol stations, parking lots and maintenance free applications
- Suitable for operation with electromagnetic gears and direct mains operation (220-240V)
- 3-Year warranty.



PRODUCT OVERVIEW

Product name	TOLEDO T8 V5 2FT 10W 1000LM 840
Technology	LED
Watt (Rated) (W)	10
Cap/Base	G13
General application	Hospitality, Logistics & Industry, Residential & Consumer
ETIM Class	EC001959
E-number FI	4740731
Warranty	5 years
Luminous flux (lm)	1000
Colour temperature (K)	4000
Light colour	Cool White
CRI (Ra)	80
Wattage (W)	10
Product Voltage (V)	230
Dimmable	No
Average life (Nominal) (h)	40000
Product EAN number	5410288282756

DATA TABLE

General data

Product name	TOLEDO T8 V5 2FT 10W 1000LM 840
Technology	LED
Watt (Rated) (W)	10
Cap/Base	G13
General application	Hospitality, Logistics & Industry, Residential & Consumer
ETIM Class	EC001959
E-number FI	4740731
Warranty	5 years

Optical data

Luminous flux (lm)	1000
Luminous flux (Rated) (lm)	1000

ToLEDo AVANT T8 CCG and AC

TOLEDO T8 V5 2FT 10W 1000LM 840
0028275

Colour temperature (K)	4000
Light colour	Cool White
CRI (Ra)	80
Lumen maintenance at end of nominal life (%)	70

Electrical data

Wattage (W)	10
Starting time (max) (s)	0.5
Warm-up time to 60% of full light (max) (s)	0.5
Product Voltage (V)	230
Lamp power factor	0.9
No. Of switching cycles before premature failures	>200000
Dimmable	No
kWh per 1000 hours burning time	10

Lifetime data

Average life (Nominal) (h)	40000
Average life (Rated) (h)	40000

Physical data

Weight (kg)	0.105
-------------	-------

Packaging

Single packaging type	Carton
Product EAN number	5410288282756
Packaging single length / height (cm)	64.5
Packaging single width (cm)	2.75
Packaging single depth (cm)	2.75
DUN14 (outer)	15410288282753
Units per outer package	10
Packaging outer length / height (cm)	68.7
Packaging outer width (cm)	22.6
Packaging outer depth (cm)	11.7

Safety data

Breakage cleaning instructions	Not applicable
Special purpose lamp	No
Suitable for household illumination	Yes
Safety message	Suitable for totally enclosed fixture