

Blind riveter

RRI-PR series



Execution:

- Industrial pneumatic-hydraulic blind riveter with container.
- Very fast and powerful, with a low air consumption per riveting operation.
- Lightweight and ergonomically designed for optimal working comfort.
- Available with multiple nose pieces for different capacities.



Art. no.	75066 391
Brand	RED ROOSTER
Manufacturer Part Number	RRI-PR40740
Connection thread	NPT 1/4 inch
Suitable for max. rivet diameter	4 mm
Stroke length	15 mm
Included in delivery	Wrench, oiler, rubber base and 2.4 mm, 3.2 mm and 4 mm nose pieces
Air consumption per impact	1.5 l
Weight of machine	1.7 kg
Model	RRI-PR40740
Inner hose diameter	9.5 mm
Max. tensile force	7000 N
Vibration	1 m/s ²
Gross Weight	2.340 kg
Product Group	7AE

EAN

8717981392469