



- NOTES:
- ENCLOSURE: NEMA TYPE 4X GRAY, POLYSTYRENE, IP66
  - IDC PUNCHDOWNS USE MOLEX 110 TYPE PUNCH-DOWN TOOL, PN 0180380001
  - WIRE TYPES:  
22-26 AWG (0.4-0.63MM) SOLID, (CABLE DIA RANGE .135-.200)  
22-26 AWG (7 STRANDS) STRANDED, (CABLE DIA RANGE .135-.200)

CUSTOMER PRODUCTION APPROVAL  
APPROVED BY: \_\_\_\_\_  
DATE: \_\_\_\_\_  
MUST BE SIGNED AND RETURNED BEFORE  
PRODUCTION WILL BEGIN.

RESTRICTED SALES DRAWING

RELEASE FOR PROD. EC NO: WNA2011-0386 DRWN: BRUPERT 2011/10/25 CHKD: JFMURPHY APPR: JFMURPHY 2012/01/18 DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)	DIMENSION STYLE	SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION
	▼=0 ▽=0	mm INCH 4 PLACES ± --- ± --- 3 PLACES ± --- ± .005 2 PLACES ± 0.13 ± .010 1 PLACE ± 0.25 ± .020 ANGULAR ± 1/2°	IN/MM	1:1	INCH	
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	DRAWN BY DATE BRUPERT 2011/10/25 CHECKED BY DATE APPROVED BY DATE JFMURPHY 2012/01/18 MATERIAL NO. 1201110001	TITLE CONVERTER BOX RJ45 TO 4 POLE MIC CAT5 SHIELDED MOLEX INCORPORATED DOCUMENT NO. RSD-120111-001			SHEET NO. 1 OF 1
		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				

RPM No. A201110765