

SOLID PC 1919 18 T



Sample photo

Order symbol: PC 1919 18 T
Product nbr: 5330069
Description: Enclosure, PC
Remarks: Transparent cover

EAN: 6418074005410
EI. number:
 Finland: 3423803
 Electric No. Italy: 7402015
 Electric No. Sweden: 2539438

Including: Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

Dimensions:	Length	Width	Height	Accessories:
mm:	188	188	180	EKHXT Mounting plate isolated
inch:	7.4	7.4	7.1	EKV 12 DIN-35 Mounting rail

Materials:	Rating:
Material: Polycarbonate	Ingress Protection (EN 60529): IP66/IP67
Base colour: RAL 7035 -light grey	Impact Resistance (EN 62262): IK08/IK09
Cover screws material: Polyamide	Electrical insulation: Totally insulated
Cover colour: Clear transparent	Halogen free (DIN/VDE 0472, Part 815): 1
Cover screws colour: Grey	UV resistance: UL 508
Gasket material: Polyurethane	Flammability Rating: UL 746C 5"
	Glow Wire Test (IEC 695-2-1) °C: 960
	NEMA Class: NEMA 1, 3, 3S, 4, 4X, 6, 6P, 12

Temperatures:	Certificates:
Temperature °C (short term): -40 ... 120 °C	SGS Fimko
Temperature °C (continuous): -40 ... 80 °C	Gost R
Temperature °F (short term): -40 ... 250 °F	
Temperature °F (continuous): -40 ... 175 °F	

Accessories:
EKHVT Mounting plate

