

Ref. **2010**

ESCARIADOR MANO

Hand Reamer
Alesoir à Main



HSS	DIN 206 B	ISO 236	Tol. H7	Tol. Agujero Hole Trou H7		Aceros <850 N/mm ² Steels/Aciers	Aluminio Aluminium Aleaciones Alloys Alliages Al Si > 10%
-----	-----------	---------	---------	---------------------------	---	---	---



D mm	L mm	I mm	a mm	Nº Art. HSS	€
1,60	44	21	1,25	74178	22,42
*1,70	44	21	1,25	74181	22,42
2,00	50	25	1,60	40379	16,80
*2,10	50	25	1,60	74190	22,42
*2,20	54	27	1,80	74193	22,42
*2,40	58	29	2,10	74199	22,42
2,50	58	29	2,10	40382	16,80
*2,60	58	29	2,10	75397	22,42
2,80	62	31	2,10	74205	22,42
3,00	62	31	2,10	40385	16,80
3,20	66	33	2,40	74214	22,42
*3,30	66	33	2,40	74217	22,42
*3,40	71	35	2,70	74220	22,42
3,50	71	35	2,70	40388	17,62
*3,60	71	35	2,70	74223	22,42
*3,70	71	35	2,70	74226	22,42
*3,80	76	38	3,00	75398	22,42
*3,90	76	38	3,00	74229	22,42
4,00	76	38	3,00	40391	16,80
*4,20	76	38	3,00	74235	23,43
*4,40	81	41	3,40	74241	23,43
4,50	81	41	3,40	40394	17,56
*4,70	81	41	3,40	74247	23,43
*4,80	87	44	3,80	74250	23,43
*4,90	87	44	3,80	74253	23,43
5,00	87	44	3,80	40397	17,56
*5,20	87	44	3,80	74259	23,43
*5,30	87	44	3,80	74262	23,43
*5,40	93	47	4,30	74265	23,43
5,50	93	47	4,30	40400	17,56
*5,80	93	47	4,30	74274	23,43
*5,90	93	47	4,30	74277	23,43
6,00	93	47	4,30	40403	17,56
*6,10	100	50	4,90	74280	23,43

D mm	L mm	I mm	a mm	Nº Art. HSS	€
*6,30	100	50	4,90	74283	23,43
*6,40	100	50	4,90	74286	23,43
6,50	100	50	4,90	40406	17,56
*6,60	100	50	4,90	75233	23,43
*6,70	100	50	4,90	74289	23,43
*6,80	107	54	5,50	74292	23,43
*6,90	107	54	5,50	74295	23,43
7,00	107	54	5,50	40409	17,56
*7,10	107	54	5,50	74298	24,73
*7,20	107	54	5,50	74301	24,73
*7,30	107	54	5,50	74947	24,73
New! 7,50	107	54	5,50	40412	18,54
*7,60	115	58	6,20	74307	24,73
*7,80	115	58	6,20	74313	24,73
8,00	115	58	6,20	40415	18,54
*8,10	115	58	6,20	74319	25,97
*8,50	115	58	6,20	40418	19,45
*8,60	124	62	7,00	74331	25,97
*8,80	124	62	7,00	74337	25,97
*8,90	124	62	7,00	74340	25,97
9,00	124	62	7,00	40421	21,39
*9,10	124	62	7,00	74343	27,11
*9,20	124	62	7,00	74346	27,11
*9,30	124	62	7,00	74349	27,11
*9,40	124	62	7,00	74352	27,11
*9,50	124	62	7,00	40424	22,32
*9,70	133	66	8,00	74358	27,11
*9,80	133	66	8,00	74361	27,11
*9,90	133	66	8,00	74364	27,11
10,00	133	66	8,00	40427	22,32
*10,10	133	66	8,00	74367	34,26
*10,20	133	66	8,00	74370	34,26
*10,30	133	66	8,00	74373	34,26
*10,50	133	66	8,00	40430	24,95

D mm	L mm	I mm	a mm	Nº Art. HSS	€
*10,60	142	71	8,00	74379	34,26
*10,70	142	71	9,00	74382	34,26
*10,80	142	71	9,00	74385	34,26
11,00	142	71	9,00	40433	24,95
*11,10	142	71	9,00	74391	36,88
*11,20	142	71	9,00	74394	36,88
*11,30	142	71	9,00	74397	36,88
*11,40	142	71	9,00	74400	36,88
*11,70	142	71	9,00	74406	36,88
*11,80	152	76	9,00	74409	36,88
*11,90	152	76	10,00	74412	36,88
12,00	152	76	10,00	40439	36,19
*12,50	152	76	10,00	40442	46,20
13,00	152	76	10,00	40445	46,20
14,00	163	81	11,00	40451	49,37
*14,50	163	81	11,00	40454	53,92
15,00	163	81	11,00	40457	53,92
*15,50	175	87	12,00	40460	58,65
16,00	175	87	12,00	40463	58,65
17,00	175	87	12,00	40469	70,62
*17,50	188	93	14,50	40472	78,86
18,00	188	93	14,50	40475	84,69
*18,50	188	93	14,50	40478	84,69
19,00	188	93	14,50	40481	84,69
20,00	201	100	16,00	40487	86,69
21,00	201	100	16,00	40493	86,69
22,00	215	107	18,00	40499	89,83
23,00	215	107	18,00	40505	93,83
24,00	231	115	20,00	40511	103,61
25,00	231	115	20,00	40517	109,98
26,00	231	115	20,00	40523	120,18
27,00	247	124	22,40	40529	131,04
28,00	247	124	22,40	40535	135,63
30,00	247	124	22,40	40547	179,51

* Ø hasta fin de existencias / while Ex-stock / jusqu'à la fin de stock