




ASTGA050MSS0006C04

Connection technology





Product characteristics

Cable plug	
M12 connector	
Free from silicone	
Free from halogen	
Gold-plated contacts	
Electrical data	
Electrical design	AC/DC
Operating voltage [V]	30 AC / 36 DC
Current rating [A]	4
Protection class	II
Environment	
Ambient temperature [°C]	-25...90
Protection	IP 68
Mechanical data	
Design	angled
Material body	housing: TPU black
Material nut	Brass; nickel-plated
Weight [kg]	0.454
Electrical connection	
Connection	PVC cable / 6 m; 2 x AWG 22 (2 x 0.34 mm ²) + 2 x AWG 24 (2 x 0.25 mm ²); Ø 6.7 mm; screened, screen not connected to the plug
Sheath colour	lilac

Wiring

- Core colours
 BK black
 BU blue
 RD red
 WH white
 screen Screen



Remarks

Pack quantity	[piece]	1
---------------	---------	---