


## MIRO TR 5VDC SK OPTO-COUPLER MODULE


IN: 5,5 VDC - OUT: 48 VDC / 2 A

Transistor 2 A  
5 V DC  
Screw terminals

### [Link to Product](#)

#### Illustration





Product may differ from Image

### Approvals



### Input

Voltage range ON	4...5.5 V DC
Voltage range OFF	0...2 V DC
Control current	6 mA
LED display	LED (yellow)

### General data

Test isolation voltage	2.5 kV
Mounting method	DIN-rail mountable (EN 60715)
Housing	Black plastic, flame retardant
Temperature range	-20...+60 °C
Dimensions H × W × D	78×6.2×65 mm

### Output

Switching voltage	5...48 V DC
Switching current per output	1 mA...2 A
Saturation voltage (across output)	max. 0.3 V DC
Leakage current (output is open)	max. 10 µA
Switching time ON/OFF	1/5 ms
Switching frequency	max. 10/1 Hz (resist./ind.)

### Commercial data

country of origin	CZ
customs tariff number	85414090
minimum order quantity	1