

Thin, versatile chemical-resistant gloves that deliver comfortable hand protection

- **Elevated comfort:** AlphaTec[®] Solvex[®] 37-675 industrial gloves' cotton flocking absorbs sweat, for greater wearer comfort
- **Augmented dexterity:** Their 15 mil/0.38mm thickness results in heightened dexterity
- **Specialized protection:** A high-performance nitrile compound composition delivers EN 374 Type A chemical resistance
- **Improved durability:** Their nitrile composition offers these AlphaTec[®] gloves greater resilience than neoprene or rubber equivalents of a similar thickness, with EN and ANSI level 4 abrasion resistance
- **Genuine versatility:** AlphaTec[®] Solvex[®] 37-675 safety gloves are suitable in both wet and dry conditions

Industries

- Aerospace
- Automotive
- Food Processing
- Food Service
- Industrial
- Oil and gas
- Agriculture
- Machinery and Equipment
- Metal fabrication
- Utilities

Applications

- Chemical processing and preparation
- Chemical Handling
- Cleaning
- Janitorial use
- Re-fuel oil fluid and diesel
- Maintenance of plant and machines



AlphaTec[®] Solvex[®]

37-675

Excellent chemical protection with a good level of grip, fit and comfort

Previously known as: Solvex[®] 37-675

Key Features

- **Cotton flocking:** Moisture-absorbent, for enhanced comfort
- **15 mil/0.38mm thickness:** PPE gloves offering comfort and dexterity
- **Nitrile compound composition:** EN 374 Type A chemical resistance

Vulcanization Chemical Accelerators

- Zinc Dibutyldithiocarbamate
- Zinc 2-mercaptobenzothiazole

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

Performance Standards



Specifications

BRAND STYLE	DESCRIPTION	SIZE	LENGTH	COLOR	PACKAGE
AlphaTec [®] Solvex [®] 37-675	Cotton Flocking, Nitrile,	6, 7, 8, 9, 10, 11	330 / 13	Green	12 pairs/polybag, 12 polybags/carton

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada Inc.
105, rue Lauder
Cowansville (Québec)
J2K 2K8, Canada
T: 1 800 363-8340
F: 1 888 267-3551

Ansell, [®] and [™] are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:
www.ansell.com/patentmarking © 2021 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.