


**ELECTRICAL TEST:**

- 1.100% OPEN SHORT MIS WIRE TEST
- 2.CONTACT RESISTANCE:3 OHM MAX
- 3.INSULATION RESISTANCE:5M OHM MIN
- 4.HI-POT TEST:DC 300V/10ms

CONSUMER ITEM	LENGTH(mm)
1	1000±30



USB Full-Featured Tye-C Standard Cable Assembly Wiring

USB Type-C Plug #1		Wire	USB Type-C Plug #1	
Pin	Signal Name		Pin	Signal Name
A1、A12、B1、B12	GND	—————	A1、A12、B1、B12	GND
A4、A9、B4、B9	VBUS	—————	A4、A9、B4、B9	VBUS
A5	CC	—————	A5	CC
B5	VCONN	—————	B5	VCONN
A6	D+	—————	A6	D+
A7	D-	—————	A7	D-
A2	TX1+	—————	B10	RX1-
A3	TX1-	—————	B11	RX1+
B10	RX1-	—————	A2	TX1+
B11	RX1+	—————	A3	TX1-
B2	TX2+	—————	A10	RX2-
B3	TX2-	—————	A11	RX2+
A10	RX2-	—————	B2	TX2+
A11	RX2+	—————	B3	TX2-
A8	SBU1	—————	B8	SBU2
B8	SBU2	—————	A8	SBU1
Shell	Shield	—————	Shell	Shield

⑦	Cable	(7/0.100S*1C+SP48/0.050T+CU+HM)*8COAX+(7/0.07T*1P+HMAM)*1C+(19/0.04T*1 1C+CU+HM)*3C+19/0.04 T*1 1C+19/0.127 7T*1C+F+PAPER+B B24/12/0.05T T OD:4.6MM	M
⑥	UV glue	UV glue yellow	g
⑤	Material	Tinplate	2PCS
④	outer molding	BLACK TPE 110P	20g
③	inner molding	BLACK TPE 110P	10g
②	Connector	Thunderbolt 3 Type-CM +E-Marker Black Insulator.Shell,Nickel plating	2PCS
①	Connector	Thunderbolt 3 Type-CM Black Insulator.Shell,Nickel plating	2PCS
NO.	PART NAME	DESCRIPTION	UNIT

APPROVED	CHECKED	DRAWING	DESIGNED	DRAWING NO.	DESCRIPTION	FINISHED PRODUCT'S FIGURE	SCALE	FIT	UNITS: MM	1RD ANGLE
		YAN	YAN				△			
							△			
							△	2020/08/27		A1
							SYM	DATE		REVISION