

Han 6HvE-gs-M25



Image is for illustration purposes only. Please refer to product description.

Part number	19 34 006 0521
Specification	Han 6HvE-gs-M25
HARTING eCatalogue	https://b2b.harting.com/19340060521

Version

Size	16 B
Version	Side entry
Cable entry	1x M25
Locking type	Double locking lever
Field of application	Special hoods/housings for Han Hv E [®] screw terminal

Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 4X 12

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained



Pushing Performance
Since 1945

Material properties

California Proposition 65 substances	Yes
--------------------------------------	-----

Specifications and approvals

CE	Yes
Approvals	DNV GL

Commercial data

Packaging size	1
Net weight	200 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140128194
eCl@ss	27440202 Shell for industrial connectors
