

Product information

78 03 140 ESD

Electronic Super Knips® XL ESD

DIN ISO 9654 DIN EN 61 340-5




- Additional 15 mm longer version: greater stability, greater cutting performance
- Durable and stainless, made of INOX surgical steel
- Cutting edge hardness approx. 54 HRC
- Precision-ground cutting edges without bevel for precise and flush cutting of the finest wires, e.g. in electronics and fine mechanics
- Precisely shaped tips cut wires close to a surface from Ø 0.2 mm
- With opening spring and opening limiter for comfortable, ergonomic and fast working thanks to automatic opening and comfortable handle width
- Extremely easy movement for fatigue-free work due to precise joint with stainless steel rivet
- INOX tool steel



General	
Article No.	78 03 140 ESD
EAN	4003773081661
Head	polished
Handles	with multi-component grips
Weight	77 g
Dimensions	140 x 50 x 15 mm
Standard	DIN ISO 9654 DIN EN 61 340-5
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details	
Cutting capacities medium hard wire (diameter)	Ø 1.2 mm
Cutting capacities soft wire (diameter)	Ø 0.2 – 2.1 mm
Jaw length (B)	12.3 mm
Jaw thickness (joint) (D)	9.2 mm
Head width (A)	15.7 mm
ESD	yes



technical change and errors excepted