


## P2663

### Pylon Probe

Product Family: Pylon



#### Mechanical:

**Test Center (mil):** 75

**Test Center (mm):** 1.91

**Overall Length (mil):** 810

**Overall Length (mm):** 20.57

**Full Travel (mil):** 90

**Full Travel (mm):** 2.29

**Recommended Travel (mil):** 67

**Recommended Travel (mm):** 1.70

#### Thermal:

**Max Operating Temp (°C):** 150

**Min Operating Temp (°C):** -55

#### Electrical:

**Current Rating (Amps):** 3

**Average DC Resistance lower than (mOhm):** 10

#### Springs

Force Type - Preload in oz (g) - Rec. Travel in oz (g) -

Spring Material

Alternate - 1.00 (28.00) - 2.00 (57.00) - Stainless Steel

Standard - 1.50 (42.00) - 3.30 (94.00) - Stainless Steel

#### Body Type

Straight

Pylon Bend

#### Materials & Finishes:

**Plunger Material:** Hardened BeCu, Gold plated

**Barrel Material:** Phosphor Bronze, Gold plated

**Ball Material:** Stainless Steel

