

Studs



Version:

- Tempered
- Rolled thread
- M 6 to M12 tempered to strength class 10.9
- M14 to M42 tempered to strength class 8.8.



Art. no.	26197 106
Thread dimension	M10
Thread length	13 mm
Thread length 2 (metric thread)	125 mm
Length	200 mm
DIN	6379

EAN-Code

4020772084844