

horizontal clamp with variable clamping height

with open clamping arm and horizontal base



Application:

Quick-action clamp with infinitely adjustable balancing function for workpieces with different clamping widths.

Version:

- galvanised and passivated.
- ergonomic, oil-resistant handle with large hand rest and soft components.
- protection against the loss of the clamping screw on the end of the clamping arm. complete with zinc-plated clamping bolt
- Size 20 clamping bolt M6 x 40 mm
- Size 50 clamping bolt M8 x 39 mm
- Size 70 clamping bolt M8 x 55 mm

Advantage:

- variable clamping height, for clamping different workpieces
- used for small lot sizes
- infinitely adjustable clamping force
- ergonomic 2 component handle
- protection against loss on clamping arm



Art. no.	26215 015
Size	20
Distance	6.1 mm
Basic length	63 mm
Elongated hole spacing	26 mm
Drill hole	5.5 mm
Drill hole 2	5.5 mm
Length 2	22 mm
Length 3	26 mm
Height	27 mm
Overall height of lower handle	70 mm
Overall height of upper handle	121 mm
Max. adjustment range	11 mm
Min. adjustment range	-7 mm
Thickness	10 mm
Distance 2	5.3 mm
Base plate length 2	12.7 mm
Length	184 mm
Min./max. elongated hole spacing	26-32 mm
Hole distance	26 mm
Base plate width	42.5 mm
Base plate length	45 mm
Tension force	2 kN
Height 2	20 mm
Height 3	35 mm

EAN-Code

4020772021955