

## Floor grating

High-pressure polyethylene

### Application:

For machine and workbench workstations.

### Execution:

- Anti-slip and non-skid, can support loads of up to 40000 kg/m<sup>2</sup>
- Highly resistant against oils, acids, solvents and alkalis
- Easy to move individually in a longitudinal or transverse direction thanks to hook connections

<b>Art. no.</b>	<b>50225 103</b>
<b>Manufacturer Part Number</b>	WD020001
<b>Surface structure</b>	Serrated
<b>Material</b>	PE - Polyethylene
<b>Length</b>	1200 mm
<b>Width</b>	600 mm
<b>Height</b>	25 mm
<b>With levelling wedge</b>	Optional
<b>Resistance against</b>	Oil, Acid, Fats, Petrol, Coolant
<b>Min. temperature resistance</b>	-10 °C
<b>Max. temperature resistance</b>	+80 °C
<b>Suitable for wet areas</b>	Yes
<b>Anti-fatigue</b>	Yes
<b>Non-slip</b>	Yes
<b>Colour</b>	Blue
<b>Gross Weight</b>	3.600 kg
<b>Product Group</b>	5AD



### EAN

5060 10353549 1