

## VOLTCRAFT® - TOP PERFORMANCE IN EVERY WAY

“Since 1982, our product range has been dynamically adapting to the constant changes in the industry. We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft’s success.”

# LEAKAGE CURRENT METER

Nº 2368174

This high-resolution leakage meter can detect currents up to 100 µA AC and features a 3 ½ digit (1999 count) LCD display and a 3.05 cm jaw opening.

It is intended for indoor use only. Do not use it outdoors. Contact with moisture, e.g. in bathrooms, must be avoided under all circumstances.

## FEATURES:

**High resolution leakage current - up to 100 µA AC// 3 1/2 digit (1999 count) LCD display//  
White LED backlight// 3.05 cm Jaw opening//**

## TECHNICAL DATA:

Display type	LCD, 3 ½ digit, 1999 count
Jaw opening	3.05 cm
AC current range	200 mA, 2 A, 200 A
AC current resolution	100 µA, 1 mA, 100 mA
AC current accuracy	±5.0% of reading + 8 digits ±5.0% of reading + 10 digits ±2.5% of reading + 10 digits
Overload indication	'OL' displayed on LCD
Battery type	2x AAA
Battery life	200 hours
Operating conditions	0 °C to +30 °C, <90 % RH (non-condensing)
	+30 °C to 40 °C, <75 % RH (non-condensing)
	+40 °C to 50 °C, <45 % RH (non-Condensing)
	<3,000 m altitude
Storage conditions	-25 °C to +60 °C, <90 % RH (non-condensing) <3,000 m altitude
Dimensions (H x W x D)	182 x 61 x 34 mm
Weight	163 g (excluding batteries)



## PACKAGE CONTENTS:

Clamp meter // 2x AAA battery // Operating instructions