

POTENTIAL TERMINAL BLOCK

4 x blue/brown

Potential terminal block
Multi color

[Link to Product](#)

Illustration



Product may differ from Image

Technical Data

Operating voltage	max. 30 V AC/DC
Total current	max. 10 A

General data

Protection	IP20
Connection	Spring clamp terminals: 0.08...2.5 mm ² (AWG 28...12)
Dimensions H x W x D	70x56x32.5 mm
Temperature range	0...+55 °C (storage temperature -40...+85 °C)

Commercial data

country of origin	DE
customs tariff number	85369010
minimum order quantity	1