



MINIZED-SWITCH-DISCONNECTOR D01 10A 400V  
3P FOR FUSE-LINKS 2-10A

| Model  |     |                                   |
|--|-----|-----------------------------------|
| product brand name                                   |     | SENTRON                           |
| Product designation                                  |     | MINIZED fuse switch disconnectors |
| <b>Design of the product</b>                         |     | as draw-out assembly              |
| General technical data                               |     |                                   |
| <b>Number of poles</b>                               |     | 2                                 |
| <b>Size of fuse system / acc. to DIN EN 60269-1</b>  |     | D01                               |
| <b>Overvoltage category</b>                          |     | 3                                 |
| Voltage  |     |                                   |
| Surge voltage resistance / Rated value               | kV  | 6                                 |
| Protection class                                     |     |                                   |
| <b>Protection class IP</b>                           |     | IP20, with connected conductors   |
| Electricity  |     |                                   |
| Current / with AC / Rated value                      | A   | 16                                |
| Main circuit   |     |                                   |
| Operating voltage / with AC / Rated value            | V   | 400                               |
| Product details                                      |     |                                   |
| Product property / sealable                          |     | Yes                               |
| Connections  |     |                                   |
| <b>Tightening torque / with screw-type terminals</b> |     |                                   |
| • minimum  | N·m | 2.5                               |
| • maximum  | N·m | 3                                 |

## Mechanical Design

|                   |    |                          |
|-------------------|----|--------------------------|
| Height            | mm | 70                       |
| Width             | mm | 54                       |
| Depth             | mm | 88                       |
| mounting position |    | any, preferably vertical |

## Certificates

### Equipment marking

- acc. to DIN EN 61346-2
- acc. to DIN EN 81346-2

F  
F

### General Product Approval

### Declaration of Conformity



## Further information

### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

### Industry Mall (Online ordering system)

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/5SG76310KK10>

### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/5SG76310KK10/all>

### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)



[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=5SG76310KK10](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SG76310KK10)

### CAX-Online-Generator

<http://www.siemens.com/cax>

### Tender specifications

<http://ausschreibungstexte.siemens.com/tiplv>



last modified:

11.03.2015