



26082306

Polyester Ex Enclosure Ex empty

75 x 230 x 56 mm

Polyester Ex Enclosure Ex empty 75 x 230 x 56 mm

[Catalogues](#)
[Operating manuals](#)
[Declaration of Conformity](#)
[Drawing](#)
[3D Data](#)

Technical data

Height	75 mm
Width	230 mm
Depth	56 mm
Material	Polyester
Colour	Graphite black (RAL 9011)
Ingress protection	IP66
Degree of protection norm	EN 60529
temperature min.	-55 °C
temperature max.	135 °C
Seal material	VMQ-(silicone)
Flammability enclosure (certification)	UL 94 V-0
Toxicity	Halogen free
Surface resistance	10^9 Ohm
Surface resistance norm	IEC 60093
Other versions on request	EMV
Special colours on request	No
Approvals	ABS, ATEX, CCOE India, EAC (TR CU), EXPLOLABS, IECEx, INMETRO, ISCVE Ukraine, UL Ex

Commercial data

Country of origin	DE
Order unit	1 Piece
Customs tariff number	39269097
Weight	0.625 kg
GTIN	4250157916235

ETIM classification

ETIM 8	EC002503
--------	----------

ROSE SYSTEMTECHNIK GMBH
Erbeweg 13-15
32457 Porta Westfalica, Germany

Tel.: +49 571 50 41-0
Fax: +49 571 50 41-6
Mail: rose@rose-pw.de

Accessories



10061105

DIN rail 15 for 02.082306