


P2447-1W

Feed Through Probe

Product Family: Pylon



Mechanical:

Test Center (mil): 225

Test Center (mm): 5.72

Overall Length (mil): 1,145

Overall Length (mm): 29.08

Full Travel (mil): 300

Full Travel (mm): 7.62

Recommended Travel (mil): 200

Recommended Travel (mm): 5.08

Thermal:

Max Operating Temp (°C): 150

Min Operating Temp (°C): -55

Electrical:

Current Rating (Amps): 20

Average DC Resistance lower than (mOhm): 10

Materials & Finishes:

Plunger Material: Hardened BeCu, Nickel plated

Barrel Material: Brass

Springs

Force Type - Preload in oz (g) - Rec. Travel in oz (g) -

Spring Material

Standard - 6.00 (170.00) - 14.00 (397.00) - Stainless Steel

